


TRIDENT





Purge Economiser - Reduces purge loss and energy according to load requirements.

- Accepts dewpoint meter signal to cycle on dewpoint temperature instead of time.
- Designed For ISO:7183-1986 (E)
- Dryer Quality Class ISO : 8573-1 : 2010 (E) class 3 (-40 ADP)
- Pressure Drop < 0.3 kg/cm² (g)
- Fabrication Code: IS 2825 / ASME SEC VIII Optional
- LCD Display
- Stainless Steel Internals
- Filter made of aluminium with differential pressure indicator
- Operating voltage : 100 253 VAC 50+5% Hz 1 Ph.



Compressed Air Dryers (Heatless)

DP V2 Series

Selection Example

Requirement	:
Flow Volume	: 480 cfm
Working Pressure	: 10 Kg / cm ²
Inlet air Temperature	: 50°c
Referring the Graphs	: Factor (T) = 0.74 Factor (P) = 1.4
Dryer capacity required	:

Flow volume	480	= 463 cfm	
Factor (T) x Factor (P)	0.74 x 1.4	- 403 CIIII	

Choose the nearest higher model i.e, Model DP-960V2

Model	Item	Inlet End	Dimensions (mm)			Weight	
Model	Code	cfm	Connection	Height	Width	Depth	Kg
DP-768V2	PD328	450	2" NB	1750	1320	850	850
DP-960V2	PD329	565	2" NB	1730	1430	850	950
DP-1440V2	PD330	850	3" NB	1865	1930	1000	1265
DP-1920V2	PD331	1130	3" NB	1990	1930	1000	1575

• For any other capacity contact factory.

• Specifications are subject to change without notification.

Specification

Maximum Operating Pressure	: 12.5 kg/cm ² (g)
----------------------------	-------------------------------

Air Inlet Temperature	: 45 ℃
Operating pressure	: 7 kg/cm ² (g)
Pre - Filter Rating	: 5 Micron
After - Filter Rating	: 1 Micron
Cycle Time	: 10 Minutes
Purge Loss	: 12 ± 1%
Outlet Conditions	: -40°C ADP


Ahmedahad

96244 36308


Principle of Operation

Drying Cycle : Moist air from the compressor is sent through the coalescing filter. Here water & oil coalesces and purges through the auto drain valve. The relatively clean air with water vapour passing through the aluminum drying tower filled with desiccant gets completely dried (up to -40°C ADP) and then passes through a built in after filter (1 micron). The desiccant fines from the towers are completely removed and clean dry air is let out through the outlet port for use.


Regeneration Cycle : During the regeneration cycle, the sudden depressurisation brings out water molecule strapped in the Desiccant pores to the surface of the beads. A small portion of dry compressed air from the drying tower then passes over the desiccant through the regeneration orifice built in the Top Block. This results in complete regeneration of the Desiccant.











Hyderabad

98854 45321



Our Other Range of Products

Timer based Auto Drain Valve • Level Sensing Auto
Drain Valve • Desiccant Dryer (Heated) • Refrigeration Dryers
 Water Separator • Submicron Filter



Trident Pneumatics Pvt Ltd

Chennai

97894 80564

5/232, K.N.G. Pudur Road, Coimbatore - 641 108, India. Ph : +91-422-2400492, 2401373 Fax : +91-422-2401376

Delhi

73977 19565

e-mail : sales@tridentpneumatics.com Website : www.tridentpneumatics.com

Bangalore

99646 23007

	Sales &
TRP	Sales & Service Outlets
K K	Service Outlets

07 / 18